

Wall-mounting Bracket AT-WLMT-010

Installation Guide

For use with Allied Telesyn Standard Size Media Converters

Allied Telesyn, Inc. www.alliedtelesyn.com

Overview

hold an Allied Telesyn Media Converter for wall-mounting. The AT-WLMT-010, shown in Figure 1, is a "shelf" style unit designed to




Figure 1. AT-WLMT-010 Wall-mounting Bracket

Copyright © 2006 Allied Telesyn, Inc. All rights reserved. No part of this publication may be reproduced without prior written permission from Allied Telesyn Inc.

Package Contents

Make sure the following items are included in the shipping package. If any item is missing or damaged, contact your Allied Telesyn sales representative for assistance.

- ☐ 10 AT-WLMT-010 brackets
- □ 10 wall-mounting kits
- ☐ This installation guide

Wall-mounting the AT-WLMT-010 Bracket

To wall-mount an AT-WLMT-010 bracket, perform the following procedure:



Caution

Make sure to mount the bracket onto a wall following the instruction printed on the bracket, with the arrows pointing up and the module retaining screw positioned on the right.

- Remove the AT-WLMT-010 bracket from the shipping package and store the packaging material in a safe place.
- Position the wall-mounting bracket on the wall and, using two Phillipshead screws (provided), secure the bracket to the wall, as shown in Figure 2.




Figure 2. Wall-mounting an AT-WLMT-010 Bracket

Once the bracket is securely mounted onto the wall, proceed to the next section.

Placing a Media Converter into the AT-WLMT-010 Bracket

To place an ATI converter into the AT-WLMT-010 bracket, perform the following procedure:

Slide the converter into the bracket tray with the bottom of the converter against the bracket and the front of the converter facing upward, as shown in Figure 3.




Figure 3. Sliding the Media Converter into the AT-WLMT-010 Bracket

Push the module retaining screw down and tighten it as shown in Figure 4. The screw threads will protrude to secure the converter in place.




Figure 4. Securing the Media Converter in the AT-WLMT-010 Bracket

The Allied Telesyn media converter is now ready for use in the AT-WLMT-010 bracket. Refer to the documentation that came with your media converter for further instructions.